





额定负载 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.
操作力 Operation force	160/250±50gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.30±0.1mm



TOTAL HEIGHT	
G	Ø
4.3	3.5
4.5	3.5
5.0	3.5
5.5	3.5
6.0	3.5
6.5	3.3
7.0	3.3
	10.5
	3.1



## PCB. 焊接图 PCB. WELDING DRAWING

## 电路图 CIRCUIT DIAGRAM

一般公差  
GENERAL TOLERANCE

≥0~2<	± 0.15
≥2~5<	± 0.25
≥5	± 0.35
角度 ANGLE	± 0.5 °

GENERAL TOLERANCE		设计 Jack Jin	图面 MM	第一视角 审核 Jacky Zhong	比例 1:1	DWG NO. 页码	型号 JK-B02123-G9.5-250	东莞市美韩电子科技有限公司 Dongguan Usakro Electronic Technoloy Co., Ltd.	
项目 ITEM	名称 DESCRIPTION							表面处理/颜色 FINISH/COLOR	
未注尺寸公差(mm)									

SIZE A4	VER R
A4	R