





额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50-60HZ) 60S min.
操作力 Operation force	160/250±50gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.30±0.1mm



TOTAL HEIGHT	
G	Ø
4.3	3.5
4.5	3.5
5.0	3.5
5.5	3.5
6.0	3.5
6.5	3.3
7.0	3.3
	10.5
	3.1

OPERATING FORCE	
VIGOR	180 ± 50gf
	250 ± 50gf
	350 ± 50gf

GENERAL TOLERANCE				
≥0~2<	± 0.15	设计 Jack Jin	图面 MM	A4
≥2~5<	± 0.25	第一视角 审核 Jacky Zhong	比例 重量	Dongguan Usakro Electronic Technology Co., Ltd.
≥5	± 0.35			
角度 ANGLE	± 0.5 °	批准 Tony Meng	页码 A/0	DWG NO. 1:1 型号 JK-B02123-G8.5-160 SIZE A4 VER R
未注尺寸公差(mm)				PART NO. 1 of 1 规格 : 6*6 防水/插件



PCB. 焊接图  
PCB. WELDING DRAWING

电路图  
CIRCUIT DIAGRAM

一般公差 GENERAL TOLERANCE	
≥0~2<	± 0.15
≥2~5<	± 0.25
≥5	± 0.35
角度 ANGLE	± 0.5 °
未注尺寸公差(mm)	

东莞市美韩电子科技有限公司

有限公司