




额定负载 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50-60HZ) 60S min.
操作力 Operation force	160/250±50gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.30±0.1mm



TOTAL HEIGHT			
G	Ø	G	Ø
4.3	3.5	7.5	3.3
4.5	3.5	8.0	3.3
5.0	3.5	8.5	3.3
5.5	3.5	9.0	3.1
6.0	3.5	9.5	3.1
6.5	3.3	10	3.1
7.0	3.3	10.5	3.1



## PCB. 焊接图

## 电路图

CIRCUIT DIAGRAM

一般公差  
GENERAL TOLERANCE

≥0~2<	± 0.15	第一视角 Jacky Jin	设计 图面 单位 MM
≥2~5<	± 0.25		审核 重量 Jacky Zhong
≥5	± 0.35	批推 Tony Meng	比例 1:1
角度 ANGLE	± 0.5 °		页码 A/1
未注尺寸公差 (mm)		版次 A/0	SIZE A4
			VER R

东莞市美韩电子科技有限公司

Dongguan Usakro Electronic Technology Co., Ltd.