







额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC:100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.
操作力 Operation force	160/250±50gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.30±0.1mm

OPERATING FORCE
V/GOR
180 ± 50gf
250 ± 50gf
350 ± 50gf

TOTAL HEIGHT		G		Ø	
G	Ø	G	Ø	G	Ø
4.3	3.5	7.5	3.3		
4.5	3.5	8.0	3.3		
5.0	3.5	8.5	3.3		
5.5	3.5	9.0	3.1		
6.0	3.5	9.5	3.1		
6.5	3.3	10	3.1		
7.0	3.3	10.5	3.1		




PCB. 焊接图

PCB. WELDING DRAWING

电路图

CIRCUIT DIAGRAM



一般公差
GENERAL TOLERANCE

≥0~2<	±0.15
≥2~5<	±0.25
≥5	±0.35
角度 ANGLE	±0.5°
未注尺寸公差 (mm)	

项目 ITEM	DESCRIPTION	MATERIAL	数量 QTY	表面处理/颜色 FINISH/COLOR
G	按钮	PPA	1	黑色
F	盖板	PPA	1	黑色
E	防尘胶	硅胶	1	黑色
D	防水层	聚酰亚胺	1	橙黄色
C	弹片	不锈钢	1	镀银
B	本体	PPA	1	黑色
A	卡件	黄铜	1	镀银

东莞市美韩电子科技有限公司			
Dongguan Usakro Electronic Technology Co., Ltd.			
1:1	DWG NO.	型号 JK-B02123T-G5.0-160JZ	SIZE A4
1 of 1	PART NO.	规格: 6*6 防水/贴片	VER R