






额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC:100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V/(50~60HZ) 60S min.
操作力 Operation force	160/250±50gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.30±0.1mm

OPERATING FORCE
VIGOR
180±50gf
250±50gf
350±50gf



PCB. 焊接图
PCB. WELDING DRAWING

电路图
CIRCUIT DIAGRAM



TOTAL HEIGHT		HEIGHT	
G	Ø	G	Ø
4.3	3.5	7.5	3.3
4.5	3.5	8.0	3.3
5.0	3.5	8.5	3.3
5.5	3.5	9.0	3.1
6.0	3.5	9.5	3.1
6.5	3.3	10	3.1
7.0	3.3	10.5	3.1

一般公差
GENERAL TOLERANCE

≥0~2<	±0.15
≥2~5<	±0.25
≥5	±0.35
角度 ANGLE	±0.5°
未注尺寸公差 (mm)	

设计 Jack Jin 审核 Jacky Zhong 批准 Tony Meng	图面 单位 比例 重量 页码 版次	A4 MM 1/1 A/0	1 : 1 DWG NO. PART NO.	型号 JK-B02123-G5-0-160 规格 : 6*6 防水/插件	SIZE A4 VER R
--	----------------------------------	------------------------	------------------------------	---	------------------------

东莞市美韩电子科技有限公司
Dongguan Usakro Electronic Technology Co., Ltd.