



8821WV-XXKP	Nylon UL94V-0	Brass	Tin Plated	8821H
Series No.	Material	Material	Metal plating	Mate with Housing

**Specifications:**

规格:

1. Voltage rating: 250VAC/DC  
额定电压: 250V AC/DC
2. Current rating: 3A AC/DC  
额定电流: 3A AC/DC
3. Withstanding voltage: 1000V AC/minute  
耐受电压: 1000V AC/分钟
4. Temperature range: -25°C~+85°C  
温度范围: -25°C~+85°C
5. Insulation resistance: 1000MΩ MIN  
绝缘电阻: 1000MΩ MIN
6. Contact resistance: 10mΩ Max  
接触电阻: 10mΩ Max

Circuits	Dimensions		
	A	B	C
2	2.50	6.10	7.50
3	5.00	8.60	10.00
4	7.50	11.10	12.50
5	10.00	13.60	15.00
6	12.50	16.10	17.50
7	15.00	18.60	20.00
8	17.50	21.10	22.50
9	20.00	23.60	25.00
10	22.50	26.10	27.50
11	25.00	28.60	30.00
12	27.50	31.10	32.50
13	30.00	33.60	35.00
14	32.50	36.10	37.50
15	35.00	38.60	40.00
16	37.50	41.10	42.50

ECN BO.		new		2015/5/3	A	瀚源
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	DATE.	REV.	
MIKEY	TOM	JERRY	PART NAME	8821WV-XXKP	UNLESS OTHERWISE SPECIFIED, TOLERANCE:	X. ±0.25
			MODEL NAME	H-8821WV-XXKP		X.x ±0.20
			3RD ANGLE PROJ	HanElectricity Co.,LTD		X.xx ±0.15
						ANGULAR ±3°
						FILE.NO.