





额定负荷	Rating	DC 12V/50mA
接触电阻	Contact Resistance	100mΩ max.
绝缘电阻	Insulation resistance	DC100V 60S 100MΩ min.
抗电强度	Dielectric strength	AC250V(50~60HZ) 60S min.
操作力	Operation force	160/250±50gf
寿命试验	Operating Life	100,000 cycles
行程	Travels	0.30±0.1mm

OPERATING FORCE	
VIGOR	
180 ± 50gf	
250 ± 50gf	
350 ± 50gf	



TOTAL		HEIGHT	
G	$\emptyset$	G	$\emptyset$
4.3	3.5	7.5	3.3
4.5	3.5	8.0	3.3
5.0	3.5	8.5	3.3
5.5	3.5	9.0	3.1
6.0	3.5	9.5	3.1
6.5	3.3	10	3.1
7.0	3.3	10.5	3.1



PCB. 焊接图


PCB. WELDING DRAWING

电路图

CIRCUIT DIAGRAM

G	按钮	PPA	1	黑色
F	盖板	PPA	1	黑色
E	防尘胶	硅胶	1	黑色
D	防水层	聚酰亚胺	1	橙黄色
C	弹片	不锈钢	1	镀银
B	本体	PPA	1	黑色
A	卡件	黄铜	1	镀银
项目 ITEM	名称 DESCRIPTION	材质 MATERIAL	数量 QTY	表面处理/颜色 FINISH/COLOR

—一般公差
GENERAL TOLERANCE



东莞市美韩电子科技有限公司					
Dongguan Usakro Electronic Technology Co., Ltd.					
设计 Jack Jin 审核 Jockey Zhong 批准 Tony Meng	图面 单位 比例 页码 版次	A4 MM 1/1 A/0	1 : 1	DWG NO.	型号 JK-B02123T-G7.5-160JZ
			1 of 1	PART NO.	规格：6*6 防水/贴片
			SIZE		
			A4	VER	R