







额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50-60HZ) 60S min.
操作力 Operation force	160/250±50gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.30±0.1mm

OPERATING FORCE	
VIGOR	
180 ± 50gf	
250 ± 50gf	
350 ± 50gf	



TOTAL		HEIGHT	
G	$\emptyset$	G	$\emptyset$
4.3	3.5	7.5	3.3
4.5	3.5	8.0	3.3
5.0	3.5	8.5	3.3
5.5	3.5	9.0	3.1
6.0	3.5	9.5	3.1
6.5	3.3	10	3.1
7.0	3.3	10.5	3.1




PCB. 焊接图

PCB. WELDING DRAWING

电路

CIRCUIT DIAGRAM



GENERAL TOLERANCE		项目 ITEM		名称 DESCRIPTION		材质 MATERIAL		数量 QTY		表面处理/颜色 FINISH/COLOR	
±0.15	±0.25	±0.35	±0.5°	设计 Jack Jin	图面 单位 MM	东莞市美韩电子科技有限公司 Dongguan Usakro Electronic Technology Co., Ltd.					
≥2~5<	≥5	角度 ANGLE	未注尺寸公差 (mm)	审核 Jacky Zhong	比例 重量 页码 版次	1:1	DWG NO.	型号 JK-B02123-G5.5-250	规格: 6*6 防水/插件		
±0.2	±0.5	第一视角		批准 Tony Meng	1/1 A/0	1 of 1	PART NO.	VER		R	