


PCB. 焊接图
PCB. WELDING DRAWING

电路图
CIRCUIT DIAGRAM



额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC-100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V/(50-60HZ) 60S min.
操作力 Operation force	160/250±50gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.30±0.1mm


OPERATING FORCE	
VI GOR	180 ± 50gf
	250 ± 50gf
	350 ± 50gf

TOTAL HEIGHT		TOTAL HEIGHT	
G	∅	G	∅
4.3	3.5	7.5	3.3
4.5	3.5	8.0	3.3
5.0	3.5	8.5	3.3
5.5	3.5	9.0	3.1
6.0	3.5	9.5	3.1
6.5	3.3	10	3.1
7.0	3.3	10.5	3.1

项目 ITEM	名称 DESCRIPTION	材料 MATERIAL	数量 QTY	表面处理/颜色 FINISH/COLOR
G	按钮	PPA	1	黑色
F	盖板	PPA	1	黑色
E	防尘胶	硅胶	1	黑色
D	防水层	聚酰亚胺	1	橙黄色
C	弹片	不锈钢	1	镀银
B	本体	PPA	1	黑色
A	卡件	黄铜	1	镀银

一般公差
GENERAL TOLERANCE

≥0-2<	±0.15
≥2~5<	±0.25
≥5	±0.35
角度 ANGLE	±0.5°
未注尺寸公差 (mm)	



东莞市美韩电子科技有限公司

Dongguan Usakro Electronic Technology Co., Ltd.

设计 Jack Jin	审核 Jacky Zhong	批准 Tony Meng	图面单位 A4	比例 1/1	重量 1/1	页码 A/0	版次
第一视角			1:1				DWG NO.
1 of 1			1 of 1				PART NO.
规格: 6*6 防水/贴片			型号: JK-B02123T-G9-0-160				SIZE A4
							Y/R
							R