



SPECIFICATIONS

- 1、Current Rating: 10A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~ +85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material: Wafer Nylon66 UL94-V0(2)
PIN Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-5003-2Y	5.00	10.00
3	HC-5003-3Y	10.00	15.00
4	HC-5003-4Y	15.00	20.00
5	HC-5003-5Y	20.00	25.00
6	HC-5003-6Y	25.00	30.00
7	HC-5003-7Y	30.00	35.00
8	HC-5003-8Y	35.00	40.00
9	HC-5003-9Y	40.00	45.00
10	HC-5003-10Y	45.00	50.00
11	HC-5003-11Y	50.00	55.00
12	HC-5003-12Y	55.00	60.00

			GENERL TOLERANCE		制 图 DRAWING	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审 核 CHECK				
			X. X	±0.30	批 准 APPROVAL	产品名称 TITLE	5.00 孔座 (白色)	版 本 REV.	A
1	初版发行		X. XX	±0.20	比 例 SCALE	产品料号 PART NO.	HC-5003-NY	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	X. XXX	±0.10	投 影 Projection	材 料 MATERIAL		页 次 SHEET	1/1
			Angle	±3.0°					