


PCB LAYOUT




SPECIFICATIONS

- 1、Current Rating: 2A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25°C~ +85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Nylon66 UL94-V0  
PIN Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-PH-2AWD-X-K	2.00	6.00
3	HC-PH-3AWD-X-K	4.00	8.00
4	HC-PH-4AWD-X-K	6.00	10.00
5	HC-PH-5AWD-X-K	8.00	12.00
6	HC-PH-6AWD-X-K	10.00	14.00
7	HC-PH-7AWD-X-K	12.00	16.00
8	HC-PH-8AWD-X-K	14.00	18.00
9	HC-PH-9AWD-X-K	16.00	20.00
10	HC-PH-10AWD-X-K	18.00	22.00
11	HC-PH-11AWD-X-K	20.00	24.00
12	HC-PH-12AWD-X-K	22.00	26.00
13	HC-PH-13AWD-X-K	24.00	28.00
14	HC-PH-14AWD-X-K	26.00	30.00
15	HC-PH-15AWD-X-K	28.00	32.00
16	HC-PH-16AWD-X-K	30.00	34.00

Ordering Information



			GENERAL TOLERANCE		制图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	审核 CHECK		产品名称 TITLE		版本 REV.	A
			X. X	±0.30	批准 APPROVAL		PH (2.0) 定位弯针			
			X. XX	±0.20	比例 SCALE		产品料号 PART NO.		单位 UNITS	mm
			X. XXX	±0.10	投影 Projection		材料 MATERIAL		页次 SHEET	1/1
1	初版发行	日期								
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE								