



- SPECIFICATIONS
- 1、Current Rating: 0.5A AC, DC
 - 2、Voltage Rating: 30V AC, DC
 - 3、Temperatuer Range: -25°C ~ +85°C
 - 4、Contract Resistance: 30mΩ Max
 - 5、Insulation Resistance: 100mΩ Min
 - 6、Withstanding Voltage: 200V AC/minute
 - 7、Material: Wafer LCP, UL94V-0
PIN Phosphoric bronze Tin-plated
Solder tad Phosphoric bronze Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-0.8-2PLT	0.80	3.80
3	HC-0.8-3PLT	1.60	4.60
4	HC-0.8-4PLT	2.40	5.40
5	HC-0.8-5PLT	3.20	6.20
6	HC-0.8-6PLT	4.00	7.00
7	HC-0.8-7PLT	4.80	7.80
8	HC-0.8-8PLT	5.60	8.60
9	HC-0.8-9PLT	6.40	9.40
10	HC-0.8-10PLT	7.20	10.20
11	HC-0.8-11PLT	8.00	11.00
12	HC-0.8-12PLT	8.80	11.80
13	HC-0.8-13PLT	9.60	12.60
14	HC-0.8-14PLT	10.40	13.40
15	HC-0.8-15PLT	11.20	14.20
16	HC-0.8-16PLT	12.00	15.00

			GENREL TOLERANCE		制图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审核 CHECK					
1			X.X	±0.30	批准 APPROVAL		产品名称 TITLE	0.8 立贴	版本 REV.	A
序号 No.			变更内容 MODIFY CONTENT	日期 MODIFY DATE	X.XX	±0.20	产品料号 PART NO.	HC-0.8-NPLT	单位 UNITS	mm
			Angle	±3.0°	投影 Projection		材料 MATERIAL		页次 SHEET	1/1