



PCB LAYOUT

Specifications:

规格:

Voltage rating: 250V AC/DC

额定电压: 250V AC/DC

Current rating: 3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage: 1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range: -40°C +105°C

温度范围: -40°C +105°C

Insulation resistance: ≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance: ≤20mΩ

接触电阻: ≤20mΩ

Material: PA6T UL94V-0

材质: PA6T UL94V-0

Plating Category: 1U"Gold

镀层: 1U"Gold

Wave soldering temperature: 255±5°C, 10S

波峰焊温度: 255±5°C, 10S

X4612 W V - XX I - C40 D28 - E60
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

1. Series No.
2. Category: W-Water
3. Welding Board Angle: V-Stright 180°
4. Row No -Pin No: XX-02P-40P
5. Plastic height: l=2.0mm
6. Pin length: C=4.0mm
7. Pin length: D=2.8mm
8. Pin length: E=6.0mm

X4612WW-XXI-C40D28-E60	PA6T	Brass	1U"Gold	X4611F
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Female

DSND	SCALE: N/A	MODEL TYPE: 2.0 BTB Connector
DWN	VIEW:	PART NO.: X4612WW-XXI-C40D28-E60
CHKD	UNIT: mm/in	DWG NO.:
APPD	SIZE: A4	X-X4612WW-XXI-C40D28-E60
		WEIGHT
		SHEET
		REVISION



XKB INDUSTRIAL PRECISION CO., LIMITED

广东星坤科技股份有限公司

日期

文件工程章

MARK

DESCRIPTION

DATE

REVISED

APPROVED

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	