





Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:5A AC/DC

额定电流: 5A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range:-40℃~+105℃



温度范围: -40℃~+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤10mΩ

接触电阻: ≤10mΩ



X3025 H F - 2xXX WS - N0

① ② ③ ④ ⑤ ⑥

1.Series No




2.Category:H-HSG

3.Category:F-Female Housing

4.Row No.Pin No:XX-2x01~2x12P

5.Special No:WS-With Base

6.Material:N0-PA66 94V-0



Recommended Panel Cut - Out
Thick:1.27mm Min/1.57mm Max

Poles	Dimensions(mm)				Poles	Dimensions(mm)			
	A	B	C	D		A	B	C	D
2x01	/	/	/	/	2x07	35.30	18.00	29.85	35.85
2x02	20.30	3.00	14.85	20.85	2x08	38.30	21.00	32.85	38.85
2x03	23.30	6.00	17.85	23.85	2x09	41.30	24.00	35.85	41.85
2x04	26.30	9.00	20.85	26.85	2x10	44.30	27.00	38.85	44.85
2x05	29.30	12.00	23.85	29.85	2x11	47.30	30.00	41.85	47.85
2x06	32.30	15.00	26.85	32.85	2x12	50.30	33.00	44.85	50.85

X3025HF-2xXXWS-N0	PA66	X3025HM	X3025TM
PART N0	Material	Suitable XKB Housing	Suitable XKB Terminal

DSND	SCALE: N/A	MODEL TYPE: 3.0mm Crimp Style Connector
DWN	VIEW:	PART NO.: X3025HF-2xXXWS-N0
CHKD	UNIT: mm/in	DWG NO.: X-X3025HF-2xXXWS-N0
APPD	SIZE: A4	

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT SHEET REVISION
1/1 A0

广东星坤科技股份有限公司

日期
文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ANGLAR	±5°			
L≤ 4	±0.2			
4<L≤ 16	±0.3			
16<L≤ 63	±0.4			
L> 63	±0.5			