





客户编码		发行日期		2023-03-23																			
客户物料编码		客户规格型号		10*12-2.7UH-0.5线																			
样如物料编码		XR10*12-2R7M-L		样如规格型号		XR10*12-2R7M-L																	
送样数量		0PCS		送样日期		2023-03-23																	
外观尺寸 mm    正视图 FRONT VIEW 顶视图 TOP VIEW 底视图 BOTTOM VIEW <tr><td>A</td><td>12.0 MAX</td><td>E</td><td>5.0±0.5</td></tr> <tr><td>B</td><td>15.5 MAX</td><td></td><td></td></tr> <tr><td>C</td><td>0.75±0.1</td><td></td><td></td></tr> <tr><td>D</td><td>15.0±2.0</td><td></td><td></td></tr> <tr><td colspan="2">标识 原理图</td><td colspan="2"></td></tr>				A	12.0 MAX	E	5.0±0.5	B	15.5 MAX			C	0.75±0.1			D	15.0±2.0			标识 原理图			
				A	12.0 MAX	E	5.0±0.5																
				B	15.5 MAX																		
				C	0.75±0.1																		
				D	15.0±2.0																		
				标识 原理图																			

绕线结构表							
绕组	起始	结束	漆包线	圈数		绕制方式	
N1	S	F	2UEW-0.5mm	6.5TS	圈数参考	平整密绕	

注意事项

1、起线，收线入磁芯槽口 2、绕线要均匀平整，不能大小边 3、用黑色少字套管

测试项目		电性范围		测试条件		测试仪器		参考值
电感量L		2.7uH±20%		at 25℃ 1KHz/0.25V		TH-2829A		2.31
直流电阻DCR		22mΩ MAX		at 25℃ 1KHz/0.25V		TH-2829A		16.40
饱和电流Isat		L≥L0*90%		at 25℃ DC 4A 1KHz/0.25V		TH2829A		

物料	规格型号			备注		生产厂家		用量	
导针	0.75mm CP线					BAICHUAN			Kg
磁芯	H3M DR2W10*12 5-7.2-5			镁锌材质		HUAZHONG			K
漆包线	QA-1(2UEW)/155					CHANGDA			Kg
套管	Φ10*15mm UL黑色扁管					XINGQI			m
	Φ11mm UL黑色扁管					XINGQI			m
接脚胶	FK661 黑胶 无卤					QI FU			Kg
无铅锡	无铅锡条					SONGBEN			Kg
作业流程									

产品包装					
包装代码					
包装标识					
包装物料					
包装尺寸					
包装说明					

标识示意图		包装示意图	

制表	黄禾香
审核	饶平
确认	钟翠兰

文件编号: CRS-20230323-7654