







| 标记<br>MARK | 更改内容<br>MODIFICATION | 日期<br>DATE | 修改<br>DRAW | 核准<br>APPROVE |
|------------|----------------------|------------|------------|---------------|
|            |                      |            |            |               |
|            |                      |            |            |               |



技术要求Specification:

- 1、材质Material: PA66 UL94V-0;
- 2、额定电流 Current rating:3.0A AC,DC
- 3、额定电压 Voltage rating: 250V AC,DC
- 4、温度范围 Temperature range:-25℃to+85℃
- 5、接触电阻 Contact resistance:≤20mΩ
- 6、绝缘电阻 Insulation resistance:≥1000MΩ
- 7、耐压 Withstand voltage:1000V AC/minute
- 8、塑件表面平整光洁,无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrs, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.



| 线数 | 型号          | 尺寸    |       |       |       |
|----|-------------|-------|-------|-------|-------|
|    |             | A     | B     | C     | D     |
| 2  | SH25001-2Y  | 2.50  | 5.70  | 3.70  | 3.70  |
| 3  | SH25001-3Y  | 5.00  | 8.20  | 6.20  | 6.20  |
| 4  | SH25001-4Y  | 7.50  | 10.70 | 8.70  | 8.70  |
| 5  | SH25001-5Y  | 10.00 | 13.20 | 11.20 | 11.20 |
| 6  | SH25001-6Y  | 12.50 | 15.70 | 13.70 | 13.70 |
| 7  | SH25001-7Y  | 15.00 | 18.20 | 16.20 | 16.20 |
| 8  | SH25001-8Y  | 17.50 | 20.70 | 18.70 | 18.70 |
| 9  | SH25001-9Y  | 20.00 | 23.20 | 21.20 | 21.20 |
| 10 | SH25001-10Y | 22.50 | 25.70 | 23.70 | 23.70 |
| 11 | SH25001-11Y | 25.00 | 28.20 | 26.20 | 26.20 |
| 12 | SH25001-12Y | 27.50 | 30.70 | 28.70 | 28.70 |
| 13 | SH25001-13Y | 30.00 | 33.20 | 31.20 | 31.20 |
| 14 | SH25001-14Y | 32.50 | 35.70 | 33.70 | 33.70 |
| 15 | SH25001-15Y | 35.00 | 38.20 | 36.20 | 36.20 |
| 16 | SH25001-16Y | 37.50 | 40.70 | 38.70 | 38.70 |

|                                      |               |                              |                        |                  |               |                |
|--------------------------------------|---------------|------------------------------|------------------------|------------------|---------------|----------------|
| TOLERANCE UNLESS OTHERWISE SPECIFIED |               | *: Inspection Item           |                        | 兆星精密电子 (深圳) 有限公司 |               |                |
| .X±0.30                              | X.° ±1°       | :Cp/Cpk and SPC Control Item | 材料<br>MATERIAL<br>PA66 |                  |               | 名称<br>TITLE    |
| .XX±0.20                             | .X° ±         |                              |                        | 料厚<br>THICK      | 编号<br>DWG NO. | ZX-XH2.54-2PJK |
| .XXX±0.10                            | .XX° ±        | 料宽<br>WIDE                   | 比例<br>SCALE            | 1:1              | 版本<br>REV.    | A              |
| 制图<br>DRAWIN                         | 审核<br>CHECKED | 日期<br>DATE                   | 角法<br>PROJ.            | 规格书              |               |                |