



产品规格书

CUSTOMER		CUSTOMER'S P/S	
TSSE DATE	2022.09.01	OUR P/N	XRCD53-101K

1. 外观尺寸图 DIMENSIOS



2. 接线图 CONNECTION (BOTTOM VIEW)




3. 绕线规格 WINDING SPEC

端子 TERMINZL	线 WIRE	圈数 TURNS	绕线方式 WINDING METHOD
S---F	Φ0.14 QA-1-180	61.5TS (REF)	CLOSED

4. 电气特性 ELECTRONICS CHARACTERISTIC

客户代码 Part No.	厂方代码 OUR Part No.	电感量 Inductance at 1kHz	直流电阻 D. C. R max.	定格电流 I. D. C max.	标识 Marking	规格代码 Sample No.
	XRCD53-101K	100uH±10%	0.88 Ω	0.62A	101	---

5. 推荐回流焊温度曲线



备注:

OPERATING TEMP. :-40°C~+85°C

INDUCTANCE DROP=35% TYP. AT IDC.

制作 DRW	审核 CHK	确认 APPD
--------	--------	---------

C. Z. W	L. J. W	0. T. Q	东莞市祥如电子有限公司
2022. 09. 01	2022. 09. 01		

试产（样）报告

(TEST REPORT)

MODEL NO: 产品型号:	XRCD53-101K	EVALUATED Q' TY: 试样数:	5PCS
--------------------	-------------	--------------------------	------

WATERIAL CODE: 磁材型号规格:	SMD 5830	TESTED DATE: 试制日期:	2022. 09. 01
---------------------------	----------	-----------------------	--------------


SPC 规格	1KHz/0.25V	1KHz/0.25V							
	LOA(S-F) uH	DCR Ω							
LOTS 序号	100uH±20%	MAX 0.88							
1	102.6	0.78							
2	101.5	0.76							
3	98.3	0.77							
4	99.2	0.78							
5	99.5	0.78							
6									
7									
8									
9									
10									
11									
12									
13									
14									
15									

(DATA) 试样情况记录

REMARK: HM2801A HM2770A HP4342A VR-114 VR115
 备注: 用100KHz 0.25V全检
 外观: OK

RESULTS: 判定:	制样员DRW	东莞市祥如电子有限公司
<input checked="" type="checkbox"/> 合格 (PASSED) <input checked="" type="checkbox"/> ROHS <input type="checkbox"/> 不合格, 改良后 (FAILED) 参照 (REF) _____	L. F. T	
	2022. 09. 01	

包装



包装方式

LEADER部	SEAL TAPE 尺寸	10cm以上
	START CARRIER TAPE尺寸	20cm以上
	TRATLER部尺寸	10cm以上
	数量	2000pcs

