



客户编码			发行日期	2023/3/31									
客户物料编码			客户规格型号	10*16-25MH-0.15线									
样如物料编码	XR10*16-253K-L		样如规格型号	XR10*16-253K-L									
送样数量	0PCS		送样日期	2023-03-23									
外观尺寸 mm				A	12.0 MAX	E	5.0±0.5						
				B	20.0 MAX								
				C	0.75±0.1								
				D	15.0±2.0								
				标识									
				原理图									
绕线结构表													
绕组	起始	结束	漆包线	圈数	绕制方式								
N1	S	F	2UEW-0.15mm	808.5TS	圈数参考	平整密绕							
注意事项													
1、起线，收线入磁芯槽口 2、绕线要均匀平整，不能大小边 3、用黑色少字套管													
测试项目	电性范围		测试条件		测试仪器	参考值							
电感量L	25mH±10%		at 25℃ 1KHz/0.25V		TH-2829A	25.40							
直流电阻DCR	27.6Ω MAX		at 25℃ 1KHz/0.25V		TH-2829A	21.20							
饱和电流Isat	L ≥ L0*90%		at 25℃ DC 105mA 1KHz/0.25V		TH2829A								
物料	规格型号			备注		生产厂家	用量						
导针	0.75mm CP线					BAICHUAN	Kg						
磁芯	H3M DR2W10*16 5-11-5			镁锌材质		HUAZHONG	K						
漆包线	QA-1(2UEW)/155					CHANGDA	Kg						
套管	Φ10*15mm UL黑色扁管					XINGQI	m						
	Φ11mm UL黑色扁管					XINGQI	m						
接脚胶	FK661 黑胶 无卤					QI FU	Kg						
无铅锡	无铅锡条					SONGBEN	Kg						
作业流程													
产品包装													
包装代码													
包装标识													
包装物料													
包装尺寸													
包装说明													
标识示意图				包装示意图									
				<table border="1"> <tr> <td>制表</td> <td>黄禾香</td> </tr> <tr> <td>审核</td> <td>饶平</td> </tr> <tr> <td>确认</td> <td>钟翠兰</td> </tr> </table>				制表	黄禾香	审核	饶平	确认	钟翠兰
制表	黄禾香												
审核	饶平												
确认	钟翠兰												