



标记 MARK.	更改内容 MODIFICATION	日期 DATE	修改 DRAW	核准 APPROVE

技术要求Specification:

- 1、材质Material: PA66 UL94V-0;
- 2、额定电流 Current rating:1.0A AC,DC
- 3、额定电压 Voltage rating: 50V AC,DC
- 4、温度范围 Temperature range:-25℃to+85℃
- 5、接触电阻 Contact resistance:≤20mΩ
- 6、绝缘电阻 Insulation resistance:≥100MΩ
- 7、耐压 Withstand voltage:250V AC/minute
- 8、塑件表面平整光洁,无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。
Plastic surface smooth and clean, no obvious burrs, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.

线数			尺寸		
	A	B	C		
2	SH12500-2Y	SH12501-2Y	1.25	4.30	3.00
3	SH12500-3Y	SH12501-3Y	2.50	5.55	4.25
4	SH12500-4Y	SH12501-4Y	3.75	6.80	5.50
5	SH12500-5Y	SH12501-5Y	5.00	8.05	6.75
6	SH12500-6Y	SH12501-6Y	6.25	9.30	8.00
7	SH12500-7Y	SH12501-7Y	7.50	10.55	9.25
8	SH12500-8Y	SH12501-8Y	8.75	11.80	10.50
9	SH12500-9Y	SH12501-9Y	10.00	13.05	11.75
10	SH12500-10Y	SH12501-10Y	11.25	14.30	13.00
11	SH12500-11Y	SH12501-11Y	12.50	15.55	14.25
12	SH12500-12Y	SH12501-12Y	13.75	16.80	15.50
13	SH12500-13Y	SH12501-13Y	15.00	18.05	16.75
14	SH12500-14Y	SH12501-14Y	16.25	19.30	18.00
15	SH12500-15Y	SH12501-15Y	17.50	20.55	19.25
16	SH12500-16Y	SH12501-16Y	18.75	21.80	20.50

TOLERANCE UNLESS OTHERWISE SPECIFIED		*: Inspection Item		兆星精密电子(深圳)有限公司	
.X±0.30	X.°±1°	(NO.)	:Cp/Cpk and SPC Control Item		
.XX±0.2	.X°±	材料	PA66	名称	MX1.25胶壳-5Pin
.XXX±0.10	.XX°±	料厚		编号	ZX-MX1.25-5PJk
制图		料宽		单位	m m
审核		日期		比例	1:1
批准		角法		版本	A
APPROVE				规格书	