



1.FIGURE AND DIMENSIONS(视图及尺寸)



XXXXXT-XXXX-XXX-AXXXX-LXXX-XXXXXT-X
① ② ③ ④ ⑤ ⑥ ⑦

- ① 系列 (Series No)
- ② Pin位 (Pin bit)
- ③ 材质 (Material) :P-PSN(磷铜先冲后镀锡)
- ④ 线规线色 (Wire gauge line color) A:(AWG20-AWG24)
Circuit:R(red)/B (black) /Y (yellow) /G (green) /
L (blue) /P (purple) /YR (orange) /W (white) /E(grey)/N (brown)
- ⑤ 线长 (Line length) L:(可定制长度)
- ⑥ 系列 (Series No)
- ⑦ 正反接或镀锡 (Front and reverse or tin-plated) Z(反接)/F (正接) TX (镀锡Xmm)

2. CIRCUIT DIAGRAM(接线图)

A	颜色	B
Circuit1	红色	
Circuit2	蓝色	
Circuit3	蓝色	
Circuit4	黑色	

3. MATERIAL(材料)

标志	料号	单用量	备注	总用量
1	X0800H-04-NOH F	2PCS		
2	X0800T-PSN	8PCS		
3	UL10064/32AWG. 红. 黑. 蓝色	1PCS/ 蓝2PCS	200MM	
总量				

⑦ 正反接或镀锡 (Front and reverse or tin-plated) Z (反接)/F (正接) TX (镀锡Xmm)							DSND		SCALE: N/A	DRAWING NO. X0800T-04-PV01-A32RLB-L200-X0800T-F			
					ANGLAR	±5°		DWN		VIEW: 	PART NO.:		
Δx					L≤ 4	±0.2		CHKD		UNIT: mm/in	DWG NO.:		
Δx					4<L≤ 16	±0.3		APPD		SIZE: A4			
Δx					16<L≤ 63	±0.4							
MARK	DESCRIPTION			DATE	REVISED	APPROVED							
REVISIONS					UNSPECIFIED TOLERANCES			XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn											1/1	A0	