



客户编码		发行日期		2023/3/31							
客户物料编码		客户规格型号		10*16-47UH-0.5线							
样如物料编码		样如规格型号		XR10*16-470K-L							
送样数量		送样日期		2023-03-23							
外观尺寸 mm		A		12.0 MAX	E 5.0±0.5						
		B		20.0 MAX							
		C		0.75±0.1							
		D		15.0±2.0							
		标识									
		原理图									
绕线结构表											
绕组	起始	结束	漆包线	圈数	绕制方式						
N1	S	F	2UEW-0.5mm	34.5TS	圈数参考 平整密绕						
注意事项											
1、起线，收线入磁芯槽口 2、绕线要均匀平整，不能大小边 3、用黑色少字套管											
测试项目	电性范围	测试条件		测试仪器	参考值						
电感量L	47uH±10%	at 25℃ 1KHz/0.25V		TH-2829A	47.60						
直流电阻DCR	86mΩ MAX	at 25℃ 1KHz/0.25V		TH-2829A	66.00						
饱和电流Isat	L ≥ L0*90%	at 25℃ DC 3A 1KHz/0.25V		TH2829A							
物料											
规格型号	备注		生产厂家	用量							
0.75mm CP线			BAICHUAN	Kg							
H3M DR2W10*16 5-11-5	镁锌材质		HUAZHONG	K							
QA-1(2UEW)/155			CHANGDA	Kg							
Φ10*15mm UL黑色扁管			XINGQI	m							
Φ11mm UL黑色扁管			XINGQI	m							
FK661 黑胶 无卤			QI FU	Kg							
无铅锡	无铅锡条		SONGBEN	Kg							
作业流程											
产品包装											
包装代码											
包装标识											
包装物料											
包装尺寸											
包装说明											
标识示意图		包装示意图									
		<table border="1"> <tr> <td>制表</td> <td>黄禾香</td> </tr> <tr> <td>审核</td> <td>饶平</td> </tr> <tr> <td>确认</td> <td>钟翠兰</td> </tr> </table>				制表	黄禾香	审核	饶平	确认	钟翠兰
制表	黄禾香										
审核	饶平										
确认	钟翠兰										