

Specifications:

规格:

1.Voltage rating:250VAC/DC
额定电压: 250V AC/DC

2.Current rating:3A AC/DC
额定电流: 3A AC/DC

3.Withstanding voltage:500V AC/minute
耐受电压: 500V AC/分钟

4.Temperature range: -55°C~+105°C
温度范围: -55°C~+105°C

5.Insulation resistance:1000MΩ MIN
绝缘电阻: 1000MΩ MIN

6.Contact resistance:30mΩ Max
接触电阻: 30mΩ Max

7.Rubber core:PBT UL94V-0
胶芯: PBT UL94V-0

8.The iron shell:SPCC-SD Nivkel Plating/Tin Plating/Gold Plating
铁壳: SPCC-SD,镀镍/镀锡/镀金

9.Terminal:Copper alloy
端子: 铜合金

Material:

材料:

7.Rubber core:PBT UL94V-0

胶芯: PBT UL94V-0

8.The iron shell:SPCC-SD Nivkel Plating/Tin Plating/Gold Plating

铁壳: SPCC-SD,镀镍/镀锡/镀金

9.Terminal:Copper alloy

端子: 铜合金

X04 XX F X X X X

① ② ③ ④ ⑤ ⑥ ⑦

① Series NO.

② Row No.Pin No:XX-09;15;25;37

③ Welding Board Angle: F-Female


④ T: Tradutional C: Car-pin

⑤ Planting Catogtry: 1:1U 2:2U 3:3U 4:5U 5:15U 6:30U 7:AuSn

⑥ Color:B-BLACK W-White BL-Blue

⑦ 1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4

NUMBER OF POSITIONS	DIMENSION			
	A±0.25	B±0.13	C±0.38	D±0.25
15	16.35	24.99	30.80	19.28
26	24.75	33.32	39.20	27.51
44	38.35	47.04	53.05	41.28
62	54.75	63.50	69.40	57.71



DSND		SCALE: N/A	MODEL TYPE: D-SUB
DWN		VIEW:	PART NO.: X04XXFXXXX
CHKD		UNIT: mm/in	DWG NO.: X-X04XXFXXXX
APPD		SIZE: A4	WEIGHT
KXB INDUSTRIAL PRECISION CO., LIMITED			SHEET
			REVISION
			1/1
			A0



ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	