




Specifications:

规格:

Voltage rating:30V AC/DC

额定电压: 30V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40°C-+105°C



温度范围: -40°C - $+105^{\circ}\text{C}$

Insulation resistance:100MΩ min

绝缘电阻: 100MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max



3~12 Pin Shape

02 Pin Shape

X1300 H - XX - N0 HF X
 (1) (2) (3) (4) (5) (6)

- 1.Series No
2.Category:H-HSG
3.Row No.Pin No:XX-02~12P
4.Material:N0-PA66 UL94V-0
5.Special No:HF-Halogen Free
6.Color:Blank-Natural ; BK-Black

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	3.15	2.85	1.30	08	10.95	10.65	9.10
03	4.45	4.15	2.60	09	12.25	11.95	10.40
04	5.75	5.45	3.90	10	13.55	13.25	11.70
05	7.05	6.75	5.20	11	14.85	14.55	13.00
06	8.35	8.05	6.50	12	16.15	15.85	14.30
07	9.65	9.35	7.80	/			

X1300H-XX-N0HF	PA66	X1300W	X1300T
X1300H-XX-N0HFBK			
PART N0	Material	Suitable XKB Wafer	Suitable XKB Terminal

DSND		SCALE: N/A	MODEL TYPE: 1.3mm Crimp Style Connector		
DWN		VIEW: 	PART NO.: X1300H-XX-N0HF		
CHKD		UNIT: mm/in	DWG NO.: X-X1300H-XX-N0HF		
APPD		SIZE: A4			
L PRECISION CO.,LIMITED			WEIGHT	SHEET 1/1	REVISION A0

					ANGLAR	±5°
Δx					L ≤ 4	±0.2
Δx					4 < L ≤ 16	±0.3
Δx					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						