




RoHS





TOTAL HEIGHT	
CODE	H
A1	1.5
A2	1.7

PCB Layout (Pattern Side)

PART NO.	
TS-1064S	
TS-1064SA	

SHRAPNEL	
CODE	MATERIAL/QTY
D2	SUS/1PCS
D4	SUS/2PCS

OPERATING FORCE	
CODE	VIGOR
B2	180±30gf
B3	250±50gf



Ⓕ	Dust film		1	Polyimide tape	
Ⓔ	Terminal		2	Phosphor bronze	Silvering
Ⓓ	Reed		2	SUS	Silvering covered
Ⓒ	Base		1	LCP	White
Ⓑ	Cover		1	SUS	Nickel plated
Ⓐ	Button		1	LCP	Black
NO.	Name	Number	Qty	Materil	Remarks

YUANDI® Yuandi Electronics Co.,Ltd

design	date	name	TACT SWITCHS
Review	date	model	TS-1064S-A□B□-D□
Approved	date		

Drawing number: Proportion 1:1 unit mm gage number A4

modify Review Approved

angle	±2°
10~30	±0.30
5~10	±0.20
~ 5	±0.10

Tolerance not specified