



Pin	A	B	C
2	2.00	6.00	2.5
3	4.00	8.00	2.50
4	6.00	10.00	3.50
5	8.00	12.00	5.50
6	10.00	14.00	7.50
7	12.00	16.00	9.50
8	14.00	18.00	11.50
9	16.00	20.00	13.50
10	18.00	22.00	15.50
11	20.00	24.00	15.50
12	22.00	26.00	15.50
13	24.00	28.00	15.50
14	26.00	30.00	15.50
15	28.00	32.00	15.50



- 技术指标:
1. 件材料: PA66 (UL-94V-0)
 2. 接触件: 黄铜镀锡
 3. 接触电阻: <10mΩ
 4. 绝缘电阻: >100MΩ
 5. 额定电压: 250V AC/DC
 6. 额定电流: 2.0A AC/DC
 7. 耐压: 能承受1000V AC/Minute
 8. 工作温度: -25~+85



ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

APPROVALS		DATE
DRAWN	G.M.Chen	2015/7/17
CHECKED		
APPROVALS		

DEALON 德之隆
ELECTRONICS CO.,LTD

TOLERANCES ARE	30 ^{±0.15} 10 ^{±0.20} 5 ^{±0.13}	±0.30 ±0.20 ±0.13	ANGLE	±2°	PART NO.	L200HY-D-XXA	SHEET	1 OF 1
					UNIT:	mm	SCALE:	1:1
					DRAWING NO.		PROJ.	