



2P宽扣



Specifications:

规格:

- 1.Voltage rating:250VAC/DC
额定电压: 250V AC/DC
- 2.Current rating:3A AC/DC
额定电流: 3A AC/DC
- 3.Withstanding voltage:1000V AC/minute
耐受电压: 1000V AC/分钟
- 4.Temperature range: -25°C--+85°C
温度范围: -25°C--+85°C
- 5.Insulation resistance:1000MΩ MIN
绝缘电阻: 1000MΩ MIN
- 6.Contact resistance:10mΩ Max
接触电阻: 10mΩ Max

Circuits	Dimensions		
	A	B	C
2	2.50	7.30	5.00
3	5.00	9.80	4.00
4	7.50	12.30	5.00
5	10.00	14.80	7.50
6	12.50	17.30	10.00
7	15.00	19.80	12.50
8	17.50	22.30	15.00
9	20.00	24.80	17.50
10	22.50	27.30	20.00
11	25.00	29.80	22.50
12	27.50	32.30	25.00
13	30.00	34.80	27.50
14	32.50	37.30	30.00
15	35.00	39.80	32.50
16	37.50	42.30	35.00

8821H-XXDP	Nylon UL94V-0(2)	8821W-D	8821T
Series No.	Material	Mate with Wafer	Mate with Terminal

new		2015/5/3		A		瀚源
ECN BO.		DESCRIPTION.		DATE.		
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1
Mikey	Tom	Jerry	PART NAME	8821H-XXDP	UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X. ±0.25
			MODEL NAME	H-8821H-XXDP		X.x ±0.20
			3RD ANGLE PROJ	HanElectricity Co.,LTD		X.xx ±0.15
						ANGULAR ±3°
						FILE.NO.