



Specifications:

规格:

- 1.Voltage rating:250VAC/DC
额定电压: 250V AC/DC
- 2.Current rating:3A AC/DC
额定电流: 3A AC/DC
- 3.Withstanding voltage:1000V AC/minute
耐受电压: 1000V AC/分钟
- 4.Temperature range: -25°C--+85°C
温度范围: -25°C--+85°C
- 5.Insulation resistance:1000MΩ MIN
绝缘电阻: 1000MΩ MIN
- 6.Contact resistance:10mΩ Max
接触电阻: \10mΩ Max

8821T-PSN	High concentration phosphorus copper	AWG#22-28	Tin Plated	8821H
Series No.	Material	Wire Range	Metal plating	Mate with Housing

new		2015/5/3	A	瀚源	
ECN BO.		DATE.	REV.		
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALE: 1/2	SCALE: 3:1
Mikey	Tom	Jerry	PART NAME 8821T-PSN MODEL NAME H-8821T-PSN 3RD ANGLE PROJ	UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X. X.x ±0.25 X.xx ±0.20 ANGULAR ±3°
			HanElectricity Co.,LTD	FILE.NO.	