



**Specifications:**

规格:

- 1.Voltage rating:250VAC/DC  
额定电压: 250V AC/DC
- 2.Current rating:3A AC/DC  
额定电流: 3A AC/DC
- 3.Withstanding voltage:1000V AC/minute  
耐受电压: 1000V AC/分钟
- 4.Temperature range: -25°C-+85°C  
温度范围: -25°C-+85°C
- 5.Insulation resistance:1000MΩ MIN  
绝缘电阻: 1000MΩ MIN
- 6.Contact resistance:20mΩ Max  
接触电阻: 20mΩ Max

Circuits	Dimensions		
	A	B	C
2	2.50	5.70	7.30
3	5.00	8.20	9.80
4	7.50	10.70	12.30
5	10.00	13.20	14.80
6	12.50	15.70	17.30
7	15.00	18.20	19.80
8	17.50	20.70	22.30
9	20.00	23.20	24.80
10	22.50	25.70	27.30
11	25.00	28.20	29.80
12	27.50	30.70	32.30
13	30.00	33.20	34.80
14	32.50	35.70	37.30
15	35.00	38.20	39.80
16	37.50	40.70	42.30

8821H-XXP	Nylon UL94V-0	8821W	8821T
Series No.	Material	Mate with Wafer	Mate with Terminal

new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	8821H-XXP	UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X.	±0.25
			MODEL NAME	H-8821H-XXP		X.x	±0.20
			3RD ANGLE PROJ	HanElectricity Co.,LTD			
						ANGULAR	±3°
						FILE.NO.	