



| REV. | ECN NO OR DESCRIPTION | REVISED | DATE |
|------|-----------------------|---------|------|
| | | | |

SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 50V AC, DC
- 3、Temperatuer Range: -25°C~+85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 100MΩ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material: Wafer PA6T/LCP, UL94V-0
PIN Phosphoric bronze Tin-plated
Solder tad Phosphoric bronze Tin-plated






TABLE:

| CSG PART NO. | Dimension mm | | |
|------------------|--------------|-------|-------|
| | A | B | C |
| WAFER-GH125W-2A | 1.25 | 5.75 | 3.75 |
| WAFER-GH125W-3A | 2.50 | 7.00 | 5.00 |
| WAFER-GH125W-4A | 3.75 | 8.25 | 6.25 |
| WAFER-GH125W-5A | 5.00 | 9.50 | 7.50 |
| WAFER-GH125W-6A | 6.25 | 10.75 | 8.75 |
| WAFER-GH125W-7A | 7.50 | 12.00 | 10.00 |
| WAFER-GH125W-8A | 8.75 | 13.25 | 11.25 |
| WAFER-GH125W-9A | 10.00 | 14.50 | 12.50 |
| WAFER-GH125W-10A | 11.25 | 15.75 | 13.75 |
| WAFER-GH125W-11A | 12.50 | 17.00 | 15.00 |
| WAFER-GH125W-12A | 13.75 | 18.25 | 16.25 |
| WAFER-GH125W-13A | 15.00 | 19.50 | 17.50 |
| WAFER-GH125W-14A | 16.25 | 20.75 | 18.75 |
| WAFER-GH125W-15A | 17.50 | 22.00 | 20.00 |
| WAFER-GH125W-16A | 18.75 | 23.25 | 21.25 |

UNLESS OTHERWISE SPECIFIED TOLERANCES

DECIMALS: X :±0.20 X.X :±0.10 X.XX :±0.05

ANGLES: X :±5° X.X :±3° X.XX :±1°

东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE: WAFER GH 1.25贴片 SMT TYPE

DWN: xiong PART NO: WAFER-GH125W-NA

CHKD: lee SCALE: 1:1 UNIT: mm

APVD: wang SIZE: A4 SHEET: 10F 1 REV: A4

CUSTOMER COPY