






Customer Drawing



- 规格参数 (Spec.):
1. 工作温度 Operating Temperature: -40°C ~ $+125^{\circ}\text{C}$.
 2. 额定电流 Current Rating: Power: 13 A MAX. Signal: 5 A MAX.
 3. 配对线径 Cable Size:
 - 3.1. Power: 14~18 AWG.
 - 3.2. Signal: 20~22 AWG.
 4. 耐电压 Dielectric Withstanding Voltage: 3000 VDC.
 5. 防护等级 Protection Class: IP67.
 6. 机械寿命 Mating Cycle: 100 Min.
 7. 对配插头见图纸 Mating plug see drawing: "HC08B-P32R"

订购信息 Ordering Information

HC18 B - S32

键位 Key
"B"

For Information on Crimp
Contacts please consult factory

Amphenol Technical Products International GZ

	第三角投影 THIRD ANGLE PROJECTION	页面 SHEET	幅面 SIZE	版次 REV.	比例 SCALE	PART NAME: HC 320XT Plug Straight Code B
		1 of 1	A3	A		
签 名 SIGNATURE		DWG NO: HC18B-S32				
制图 DRAWN	图 号 REV	UNLESS OTHERWISE SPECIFIED				
审核 CHECKED	图 号 REV	1) All dimensions are in metric(mm).				
批准 APPROVAL	图 号 REV	2) Tolerances are as follows:				
		0 PL DEC ± 1.00				
		1 PL DEC ± 0.50				
		2 PL DEC ± 0.50				
		Angles $\pm 1^{\circ}$				
		CART PART #: N/A				
		CART REV. -				