
Piezoelectric SMD Sounder







Application

For consumer and medical market.

> Consumer : Remote controller

Mobile printer

Payment terminal

Digital still camera etc...


Medical : Blood glucose meter

Thermometer etc...




Feature and Structure

- ✓ Small, thin and lightweight 9.0mm x 9.0mm x 1.9mm 44% less than current one
- √ Low power consumption
- √ The piezo based brings in noiseless because of magnet less



Sound Pressure Level




Specifications

Global Part Number	PKMCS0909E4000-R1
Sound Pressure Level	65dB min.
Measure Condition of Sound Pressure Level	±1.5 Vo-p,4.0kHz,square wave,10cm
Maximum Input Voltage	±12.5Vo-p max.
Operating Temperature Range	-40 to +85°C
Storage Temperature Range	-40 to +85°C
Drive Type	External-Drive

Dimensions and Land pattern

(in mm)

PKMCS Series



- * The location of open hole is not specified.
- * Tol. : ±0.2mm