







Specifications:

规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:2A AC/DC
额定电流: 2A AC/DC
Withstanding voltage:1200V AC/minute
耐受电压: 1200V AC/分钟
Temperature range:-40°C~+125°C
温度范围: -40°C~+125°C
Insulation resistance:1000MΩ min
绝缘电阻: 1000MΩ Min
Contact resistance:10mΩ Max
接触电阻: 10mΩ Max



X25072 H I - XX F XX - PT SN
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- Series No
- Category:H-HSG
- Category:I-Punctured type
- Row No,Pin No:XX-02~17 Pin
- Appearance type:F Type
- Spacer bar:For example 12-Keying between pin 1 and pin 2
23-Keying between pin 2 and pin 3...When the pin number is above 10, use the letters A ,B C...A for 10,B for 11...
- Blank-No Keying
- Material:PT-PBT ;N0-PA66 UL 94V-0
- Platig:SN-Plated Tin ; V01-Gold Flash;V03-Gold 3u;
V15-Gold 15u;V30-Gold 30u

Poles	Dimensions(mm)		Spacer bar		
	A	B	C	D	
			00	/	/
02	7.40	2.50	12	7.40	2.50
03	9.90	5.00	23	9.90	5.00
04	12.40	7.50	34	12.40	7.50
05	14.90	10.00	45	14.90	10.00
06	17.40	12.50	56	17.40	12.50
07	19.90	15.00	67	19.90	15.00
08	22.40	17.50	78	22.40	17.50
09	24.90	20.00	89	24.90	20.00
10	27.40	22.50	9A	27.40	22.50
11	29.90	25.00	AB	29.90	25.00
12	32.40	27.50	BC	32.40	27.50
13	34.90	30.00	CD	34.90	30.00
14	37.40	32.50	DE	37.40	32.50
15	39.90	35.00	EF	39.90	35.00
16	42.40	37.50	FG	42.40	37.50
17	44.90	40.00	GH	44.90	40.00

X25072HI-XXFXX-PTSN	AWG24~22	Phosphor	X25072W
PART NO	Wire Range	Material(Pin)	Suitable XKB Wafer

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	2.5mm Pitch Rast Connector
CHKD	UNIT: mm/in	PART NO.:
APPD	SIZE: A4	X25072HI-XXFXX-PTSN
		DWG NO.:
		X-X25072HI-XXFXX-PTSN



XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0

					ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						