



SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- 4、Contact Resistance: $20\text{m}\Omega$ Max
- 5、Insulation Resistance: $1000\text{M}\Omega$ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Nylon66, UL94V-0

编 号	尺寸 (mm)		
	A	B	C
A2009-2X02Y	2.00	07.00	3.00
A2009-2X03Y	4.00	09.00	3.00
A2009-2X04Y	6.00	11.00	5.30
A2009-2X05Y	8.00	13.00	6.30
A2009-2x06Y	10.00	15.00	8.30
A2009-2x07Y	12.00	17.00	8.30
A2009-2x08Y	14.00	19.00	12.30
A2009-2x09Y	16.00	21.00	12.30
A2009-2x10Y	18.00	23.00	12.30
A2009-2x11Y	20.00	25.00	16.30
A2009-2x12Y	22.00	27.00	16.30
A2009-2x13Y	24.00	29.00	16.30
A2009-2x14Y	26.00	31.00	16.30
A2009-2x22Y	42.00	47.00	16.30

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENEAL TOLERANCE		制图 DRAWING	钱岳生 2013、07、01		料号 PART NO.	A2009-NY		版本 REV.	A
			X.±0.25	X.*±2'	审核	张名		品名 TITLE	PHB孔座		页次 SHEET	1/1
			.X±0.20	.X'±1'	核准	张名		客户料号 CUTM. NO.				
			.XX±0.15	.XX'±0.5'	APPROVAL	2013、07、05		深圳市金航标电子有限公司		www.kinghelm.com.cn		
			.XXX±0.10	.XXX'±0.5'	单位 UNITS	MM	比例 SCALE	1:1	KH-A2009-2X13Y		0755-28190160	