



PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- 4、Contact Resistance: $20\text{m}\Omega$ Max
- 5、Insulation Resistance: $1000\text{M}\Omega$ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer Nylon66, UL94V-0
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
A2508-2X04A	7.50	15.00
A2508-2X05A	10.00	17.50
A2508-2X06A	12.50	20.00
A2508-2X07A	15.00	22.50
A2508-2X08A	17.50	25.00
A2508-2X09A	20.00	27.50
A2508-2X10A	22.50	30.00
A2508-2X11A	25.00	32.50
A2508-2X12A	27.50	25.00
A2508-2X13A	30.00	37.50
A2508-2X14A	32.50	40.00
A2508-2X20A	47.50	55.00

GENERAL TOLERANCE		制图	钱岳生		料号	A2508-2XNA		版本
X.±0.25	X.*±2'	DRAWING	2013、07、01		PART NO.			REV.
.X±0.20	.X'±1'	审核	张 名		品 名	XA双排直针		页次
.XX±0.15	.XX'±0.5'	CHECK	2013、07、03		TITLE	WAFER DIP TYPE		SHEET
.XXX±0.10	.XXX'±0.5'	核准	张 名		客户料号			1/1
UNITS	MM	APPROVAL	2013、07、03		CUTM. NO.	深圳市金航标电子有限公司		
SCALE	1:1					www.kinghelm.com.cn		
						KH-A2508-2X09A		0755-28190160