


REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN			



**NOTES:**

- 1. ELECTRICAL:**
- 1.1. VOLTAGE RATING:DCV 300V 10MS
  - 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
  - 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
  - 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
  - 1.5. IT SHOULD BE NO ANY OPENS/SHORT, MISWIRING AND INTERMITTENT FAILURES.
- 2. MATERIAL:**
- 2.1. SEE TABLE
- 3. ALL COMPONENTS ARE ROHS COMPLIANT.**

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
①	同轴线	RF0.81黑色线, OD: 0.81mm	AS
②	接头	SMA母头母针, 分体, 11牙, 镀金	1
③	套管	黑色热缩套管, OD:2.0MM	AS

深圳市金航标电子有限公司 [www.kinghelm.com.cn](http://www.kinghelm.com.cn)

型号: KH-122-081SMA-160 0755-83044319

ALL DIMENSION ARE IN MM		DRAWN	DATE	SMA / F TO OPEN L=160MM	
		Jamy	2020-06-15	SIZE	REV
COMPUTER GENERATED IN SOLIDWORKS		ENG.		B	A
DO NOT SCALE THIS DRAWING		MFG.		SCALE: Free	
PROJECTION		Q.A.		TYPE	SHEET 1 OF 1
GENERAL TOLERANCE FOR ANGLES X.X ± 1° X.XX ± 0.3 X.XXX ± 0.25 X.XXXX ± 0.150					

CUSTOMER P/N:

D

4

3

2

1

C

B

A

4

3

2

1

D

C

B

A