





注：本板为禁止运输、复制、编辑文件，以及利用其内容进行交流



2 PIN




技术指标:

- 1、器件-表面贴片, 无毛刺、明显收缩、缺角、翘皮等现象;
- 2、温度范围: -25° C~85° C;
- 3、额定电压: 250V, AC, DC(等效);
- 4、接触电阻: ≤0.03Ω;
- 5、绝缘电阻: ≥1000MΩ;
- 6、耐压: 1000V, AC/minute.


ROHS管理规范:
1、禁止使用含有ROHS指令所限制的物质。
2、对定的SGS或TSMH厂家的ICP-ASS封装、不可确定物质成分为差, 有效期一年。

How to order



REV	ECN NO.	CONTENT	CHK	DATE
2				
1				
0				

CKT	dim A	dim B	dim C	dim D
2	2	4.9	8	6.4
3	4	6.9	10	8.4
4	6	8.9	12	10.4
5	8	10.9	14	12.4
6	10	12.9	16	14.4
7	12	14.9	18	16.4
8	14	16.9	20	18.4
9	16	18.9	22	20.4
10	18	20.9	24	22.4
11	20	22.9	26	24.4
12	22	24.9	28	26.4
13	24	26.9	30	28.4
14	26	28.9	32	30.4
15	28	30.9	34	32.4
16	30	32.9	36	34.4



嵌合图面

GENERAL TOLERANCES

0.X	±0.25	X.°	±3°
0.XX	±0.12		
0.XXX	±0.05	X.X°	±0.5°

序号	名称	材料	数量	备注
1	贴片	120°C (MAX-40)	1	
2	贴片		2	
3	贴片		2	

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG	CHK	DATE	DATE	SCALE	SHEET/OF
APP	DATE			1:1	A4
	NAME				

MAXXU 慈溪市迈旭电子有限公司

CIXI MAXXU ELECTRONICS CO.,LTD
MXP H-2.0-XXP-W/G1