


REV. NUMBER		DESCRIPTION		DWN	CHK	DATE
A		DESIGN				



cable loss 小于等于0.3dbm@0-6G

- NOTES:
- ELECTRICAL:
 - VOLTAGE RATING:DCV 300V 10MS
 - CONDUCTANCE RESISTANCE:3.0 OHM/MAX.
 - INSULATION RESISTANCE: 5.0M OHM/MIN.
 - THE CABLE SHOULD BE 100% ELECTRICAL TEST
 - IT SHOULD BE NO ANY OPENS/SHORT, MISWIRING AND INTERMITTENT FAILURES
 - MATERIAL:
 - SEE TABLE
 - MECHANICAL:
 - SMA PULL FORCE: 12.0KGS.
 - ALL COMPONENTS ARE ROHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
④	套管	黑色热缩套管, OD:2.0MM	AS
③	接头	同2	1
②	接头	SMA母头内孔, 分体, 11牙, 镀金	1
①	同轴线	RG316黑色线,OD: 4 mm	AS

深圳市金航标电子有限公司 WWW.BDS666.COM
 KHA(RG316) -TX650-SMA 0755-83044319

ALL DIMENSION ARE IN MM	DRAWN Jamy	DATE 2018/05/04	TITLE
COMPUTER GENERATED IN SOLIDWORKS	ENG.	MFG.	RF CABLE
DO NOT SCALE THIS DRAWING	Q.A.		I-PEX 1.13 TO SMA /F L=650 MM
PROJECTION	GENERAL TOLERANCE FOR ANGLES XX XXX XXXX ± 1° ± 0.3 ± 0.25 ± 0.150		SIZE Number
CUSTOMER PIN:			B
			SCALE: Free
			TYPE
			SHEET 1 OF 1
			REV A

4 3 2 1

A B C D

4 3 2 1