



**RECOMMENDED PCB LAYOUT  
COMPONENT SIDE VIEW**

**SPECIFICATION**  
 Current Rate: 3Amp  
 Contact Resistance: 20mΩ MAX.at DC 1A  
 Insulation Resistance: 1000MΩ MIN.atDC500V  
 Dielectric Strength: AC500V PER minute  
 Operation Temperature: -40°to +105°

**MATERIAL**  
 Insulator: Polyester , UL94V-0  
 Standard: PA6T  
 CONTACT: Phosphor Bronze  
 Contact plated: Gold Over Nickel  
 Color: Black

TOLERANCE TABLE	
.0	± 0.20
.00	± 0.10
.000	± 0.05

APPROVED:	DATE:	TITLE: 深圳市灿科盟实业有限公司 kmtw CHANKEMENG INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: 220S-2*4P H=5.0 封闭式 (U型)			
DRAWN:	DATE:	CLIENT P/N	21UB08PBB101	UNIT	mm
LYF	2021-04-01	SCALE	free	REV.	A
		FILE NO.	S049000266		