




THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.

Customer Drawing



6		7		8	
REV		ZONE		ECO	
DESCRIPTION		DATE		BY	
A		--		--	
B		--		--	
C		--		--	



- 注(NOTES):
- 对配母端直径 Mating contact diameter:1.6mm
 - 额定电流 Current rating: 13A
 - 端子类型 Terminatin type: Crimp
 - 压线规格 Wire size: AWG16~18
 - 电镀信息 Plating specification:
镍底镀锡 Tin over nickel
 - 材料规格 Material specification:
6.1. 端子: 铜合金
Contact body: Copper alloy
6.2. 外套: 不锈钢
Outer spring: Stainless steel
 - 符合ROHS
ROHS compliant

AMPHENOL		Amphenol Technical Products International GZ					
第三角投影 THIRD ANGLE PROJECTION		页 面 SHEET	幅 面 SIZE	版 次 REV.	比 例 SCALE	PART NAME: HC Contact 16#Pin AWG16~18	
1 OF 1		A3	C	DWG NO: HCTM21504		CUST PART #: N/A	
签 名 SIGNATURE		日期 DATE		UNLESS OTHERWISE SPECIFIED		CUST REV. -	
制 图 DRAWN		JS		1) All dimensions are in metric(mm).			
审 核 CHECKED		YM		2) Tolerances are as follows:			
批 准 APPROVAL		JL		1 PL DEC ± 1.00			
				2 PL DEC ± 0.50			
				3 PL DEC ± 0.20			
				Angles $\pm 1^\circ$			