





注：本板为禁止转输、复制、编辑文件，以及利用其内容进行交流



PCB Layout

Pitch Range In mm		Nominal Dimension Range In mm		Pitch Range In mm		Nominal Dimension Range In mm		Pitch Range In mm		Nominal Dimension Range In mm	
Over 6	Over 10	Over 10	Over 30	Over 60	Over 100	Over 150	Over 150	Over 6	Over 10	Over 10	Over 30
TO 6	TO 10	TO 24	TO 30	TO 60	TO 100	TO 150	TO 150	TO 6	TO 10	TO 24	TO 30
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±0.15	±0.20	±0.30	±0.30

NOTES1:

UL Standard

1.

Use group	B	C	D
Rated Current	15A	/	10A
Rated Voltage	300V	/	300V

2.withstanding voltage: AC2500V/1min

3.Torque value: M3, 4, 4.3Lb.in

4. Wire range: 22~14AWG

IEC Standard

1.

Pollution Degree	3	2	2
Overvoltage Category	III	II	I
Rate Impulse Voltage(KV)	/	/	/
Rate Voltage(V)	/	250V	/
Rate Current(A)	/	15A	/

2. Torque value: M3, 0.5Nm

3.wire range: 10~2.5mm²

NOTES2:

1.Housing: PA66(UL94V-0)

2.Solder Pin: Copper alloy(Sn Plated)

3.Spring: Stainless Steel

4.Screw: Steel(M3,Zn Plated)

NOTES3:

1.Pitch: 7.5mm Poles: 02-24P

2.Stripping length: 6-8mm

3.Operating temperature: -40℃~+105℃

4.RoHS Compliance

How to order

MX360 - 7.5 - XXP - XXXX - XX - X - X

产品型号

间距

颜色:

极数

颜色: 01:常规颜色

灰色:GY

橙色:OE

02-99:

蓝色:BU

红色:RD

定制颜色

黑色:BK

透明色:TT

绿色:GN

黄色:YW

透明色:TT

白色:WE

Cu:铜方块

2.P:PS平头十字螺丝

Fe:铁方块

透明色:TT

白色:WE

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG.	CHK	DATE	23.08.19	UNITS	MM
CHK	DATE	SCALE	1:1	A4	1/1
APP.	DATE	NAME	MX360-7.5-XXP		
CIXI MAIXU ELECTRONICS CO.,LTD					
慈溪市迈旭电子有限公司					
DWGNO.					