







ROHS



PCB Layout

SPECIFICATIONS

1. Rating : DC 30V 1.0A
2. Contact Resistance: $\leq 50m\Omega$
3. Insulation Resistance:
 $\geq 1000m\Omega$ Min DC250V
4. Operating Temperature Range:
 $-40^{\circ}C+85^{\circ}C$

U-G-04WD-W-01	Housing&Black(黑色)
U-G-04WD-W-02	Housing&White(白色)
U-G-04WD-W-03	Housing&Beige(米黄色)

③	Shell	——	1	SPCC	Ni Plated	——	
②	Contact	——	4	Copper Alloy	Ag Plated	——	
①	Housing	——	1	Nylon	White/Black	——	
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK	
APPROVALS			DATE	HRO 宏睿® ELECTRONICS CO.,LTD			
DRAWN		LIUCAN	2019.04.18				
CHECKED				TITLE:	USB CONNECTOR		
APPROVALS				PART NO.	U-G-04WD-W-□□		
D.	TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 
		10~30	±0.25				
		5~10	±0.20				
		~ 5	±0.15				
		±2'		DRAWING NO.	——	SHEET 1 OF 1	

NEW						
DESCRIPTION.						
—	A	—	—	—	—	—
ECN NO.	REV.	DATE.	CHANGE.	CHECK.	APPRO.	