





- NOTE:
- 1.Rating1: 3A DC48V
 - Rating2: 2A AC125V
 - 2.Operating froce:150gf MAX
 - 3.Electric Life:10,000
 - 4.Mechanical Life:30,000
 - 5.Ingress protection:IP67



⑧	Sealing mat	—	1	TPE	—	—
⑦	Sealing cap	—	1	Silicone Rubber	—	—
⑥	Shrapnel	—	1	Beryllium copper	Plating silver	—
⑤	Contact	—	1	Ag	—	—
④	Terminal	—	3	Brass(0.50t)	Plating silver	—
③	Plunger	—	1	PBT	Black	—
②	Case	—	1	PBT	Black/White	—
①	Cover	—	1	PA	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS			DATE	HRO 韩荣®		
DRAWN		LIUCAN	2023.8.14	ELECTRONICS CO.,LTD		
CHECKED				TITLE: MICRO SWITCHES		
APPROVALS				PART NO.		
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1
		10~30	±0.20			
		5~10	±0.15	±2°	DRAWING NO.	PROJ: 1 OF 1
		~ 5	±0.10			

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.