





ROHS

Typical Specifications :

1. Rating : DC 12V 50mA
2. Insulation resistance: $\geq 100M\Omega$
3. Withstand voltage: AC 250V/1min
4. Life:300,000 Cycles.
5. Ingress protection: IP67



Circuit Diagram

NO.1	
PART NO	H
C	3.1
D	3.5
A	3.8
G	4.3
B	4.5
M	4.8
F	5.0
N	5.2
E	5.5

NO.2	
PART NO	vigor
3	180±40
4	250±50

NO.3-NO.4	
PART NO	NOTE
01~99	SERIAL NUMBER

⑤	Terminal	—	4	Brass		Plating silver	_____
④	Contact	—	1	F.Ag/SUS			
③	Base	—	1	PPA		Black	
②	Cover	—	1	SUS			
①	Keystoke	—	1	Silica gel		Blue	
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK	

APPROVALS		DATE		TITLE:	
DRAWN	LIUCAN	2022.7.22		TACT SWITCHS	
CHECKED					

APPROVALS		PART NO.		TITLE:	
DRAWN		LIUCAN		TACT SWITCHS	
CHECKED					
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1
	10~30	±0.20			PROJ:
	5~10	±0.15	±2°	DRAWING NO.	—
	~ 5	±0.10		SHEET	1 OF 1

ECN NO.	REV.	DATE.	NEW	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
—	A	—					

HIRO
ELECTRONICS CO.,LTD