





ROHS

韓泰

NO.1	
PART NO	H
B	4.5
C	5
D	5.5
E	6
F	6.5
G	7

NO.2	
PART NO	vigor
3	180 ± 30
4	250 ± 30

NO.3-NO.4	
PART NO	NOTE
01~99	SERIAL NUMBER

ITEM	PART NAME	TER'NO.	QTY.	APPROVALS		DATE	REMARK
				TERMINAL	CONTACT		
⑤	Terminal	—	2	Brass(0.30t)	Plating silver		
④	Contact	—	1	F.Ag/SUS	Plating silver		
③	Base	—	1	Nylon	Black		
②	Cover	—	1	Brass	Plating Sn		
①	Keystoke	—	1	Nylon	Black		

APPROVALS		DATE		TITLE:	
DRAWN		LIUCAN		2022.12.7	
CHECKED					

APPROVALS		PART NO.		TITLE:	
APPROVALS		K2-1102SE-□□SW-□□			
TOLERANCES ARE	30~以上	± 0.30	ANGLE	UNIT: mm	SCALE: 1:1
	10~30	± 0.20			PROJ:
	5~10	± 0.15	$\pm 2^\circ$	DRAWING NO.	SHEET 1 OF 1
	~ 5	± 0.10			

ECN NO.	A	REV.	DATE.	NEW	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
—	—	—	—	—	—	—	—	—

HIRO
ELECTRONICS CO.,LTD