





ROHS

Typical Specifications

- 1.Rating : DC 12V 50mA
- 2.Contact Resistance: $\leq 100m\Omega$
- 3.Insulation Resistance: $\geq 100m\Omega$
- 4.Operating Force: $250\pm 50gf$
- 5.Travel: $0.20\pm 0.1mm$
- 6.Life : 50,000 Cycles


(R)

PCB Layout(Pattern side)



NO.1	
PART NO	H
A	4.3
B	4.5
C	5.0
E	6.0
G	7.0
I	8.0

NO.2~NO.3	
PART NO	NOTE
01~99	SERIAL NUMBER



Circuit Diagram

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL		FINISHING	REMARK
				COVER	SUS		
⑤	Cover	—	1	SUS	—	—	—
④	Keystoke	—	1	PPA	Black	—	—
③	Contact	—	1	F.Ag/SUS	Plating silver	—	—
②	Base	—	1	PPA	Black	—	—
①	Terminal	—	2	Brass(0.3t)	Plating silver	—	—

APPROVALS		DATE	TITLE: TACT SWITCHS		
DRAWN	LIUCAN	2021.9.28	PART NO. K2-1101SP-□4SW-□□		
CHECKED	—	—			
APPROVALS	—	—			

TOLERANCES ARE	30~以上	± 0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:
	10~30	± 0.20				
	5~10	± 0.15				
	~ 5	± 0.10	$\pm 2^\circ$	DRAWING NO. —	—	SHEET 1 OF 1

—	A	—	NEW	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.

HRD

ELECTRONICS CO.,LTD