



ROHS





Typical Specifications :
1. Rating : DC 12V 50mA
2. Life:300,000 Cycles Min.



Circuit diagram



PCB Layout(Pattern Side)



NO.1		
PART NO	H	L
C	5.15	2.3
H	7.25	4.4

NO.2	
PART NO	vigor
3	180±30
4	250±30

NO.3	
PART NO	MATERIAL/QTY
S	SUS/1PC

NO.4-NO.5	
PART NO	NOTE
01~99	SERIAL NUMBER

⑦	Pressure pad	—	1	PPA	Black	—
⑥	Rubber pad	—	1	Silica gel	Black	—
⑤	Terminal	—	2	Brass(0.30t)	Plating silver	—
④	Base	—	1	PA6T	Black	—
③	Contact	—	1	F.Ag/SUS	—	—
②	Cover	—	1	SUS	Plating silver	—
①	Keystoke	—	1	PPA	White	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE		HRO® ELECTRONICS CO.,LTD		
DRAWN		LIUCAN	2023.3.2				
CHECKED				TITLE:		TACT SWITCHS	
APPROVALS				PART NO.		K2-1102HD-□□SW-□□	
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	
	10~30	±0.20					
	5~10	±0.15					
	~ 5	±0.10					
DRAWING NO.						SHEET 1 OF 1	

—	A	—	NEW	—	—	—
ECN NO.	REV	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.