





ROHS




P.C.B layout





K9-1267U-L

K9-1267U-R



Circuit Diagram



Part No. (料号)
K9-1267U-R
K9-1267U-L

- NOTE:
- 1.Rating:DC30V 0.1A
 - 2.OP:10.70±0.8
 - 3.Operating froce:30±15gf
 - 4.Mechanical Life:300,000

⑦	Lever	—	1	SUS	—	—
⑥	Shrapnel	—	1	Phosphor copper	—	—
⑤	Contact	—	1	Silver Alloy	—	—
④	Terminal	—	3	Brass(0.52t)	Plating silver	—
③	Housing	—	1	PBT	White	—
②	Knob	—	1	PBT	White	—
①	Cover	—	1	PBT	Black	—

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
------	-----------	---------	------	----------	-----------	--------

APPROVALS			DATE	 ELECTRONICS CO.,LTD MICRO SWITCHS		
-----------	--	--	------	--	--	--

DRAWN	LIUCAN	2021.10.16				
-------	--------	------------	--	--	--	--

CHECKED			TITLE:			
---------	--	--	--------	--	--	--

APPROVALS			PART NO.			
-----------	--	--	----------	--	--	--

TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:
----------------	-------	-------	-------	----------	------------	-------

10~30	±0.20	±2'	DRAWING NO.	SHEET	1 OF 1
-------	-------	-----	-------------	-------	--------

5~10	±0.15				
------	-------	--	--	--	--

~ 5	±0.10				
-----	-------	--	--	--	--

NEW	CHANGE.	CHECK.	APPRO.
ECN NO.	REV.	DATE.	DESCRIPTION.