



ROHS



Circuit diagram

NO.1	
PART NO	H
A	3.8
B	4.3
C	4.5
D	5

NO.2	
PART NO	vigor
3	180±30
4	250±40

NO.3-NO.4	
PART NO	NOTE
01~99	SERIAL NUMBER

Travel: 0.20±0.1mm
Life: 100,000 Cycles

⑤	Terminal	—	2	Brass(0.30t)	Plating silver	—
④	Contact	—	1	F.Ag/SUS	—	—
③	Base	—	1	PPA	Black	—
②	Cover	—	1	Brass	Plating Sn	—
①	Keystoke	—	1	Silica gel	Blue	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE	ELECTRONICS CO.,LTD			
DRAWN	LIUCAN	2021.5.19	TACT SWITCHES			
CHECKED			TITLE:			
APPROVALS			PART NO.	K2-1109SG-□□SW-□□		
TOLERANCES ARE		30~以上 10~30 5~10 ~ 5	±0.30 ±0.20 ±0.15 ±0.10	ANGLE	UNIT: mm	SCALE: 1:1
		~ 5	±2'	DRAWING NO.		PROJ:
						SHEET 1 OF 1

—	A	—	NEW	—	—	—
ECN NO.	REV	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.