






Circuit Diagram



NOTE:
Rating:DC 12V 50mA
Operating Force:100±30gf
Travel: 0.25±0.1mm
Life:1,000,000 Cycles

⑥	Internal key	—	1	Silica gel	Grey	—
⑤	Knob	—	1	Nylon	Yellow	—
④	Cover	—	1	Nylon	Black	—
③	Terminal	—	2	Brass	Plating silver	—
②	Contact	—	1	F.Ag/Brass	Plating silver	—
①	Base	—	1	Nylon	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE		 ELECTRONICS CO.,LTD	
DRAWN	LIUCAN		2022.8.27			
CHECKED					TITLE:	TACT SWITCHES
APPROVALS					PART NO.	K2-1819DP
TOLERANCES ARE			30~以上	±0.30	ANGLE	UNIT: mm
			10~30	±0.20		
			5~10	±0.15	±2'	SCALE: 1:1
			~ 5	±0.10		
					DRAWING NO.	
						SHEET 1 OF 1

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.