




Specifications:

规格:

Voltage rating:400V AC/DC

额定电压: 400V AC/DC

Current rating:10A AC/DC

额定电流: 10A AC/DC

Withstanding voltage:1800V AC/minute

耐受电压: 1800V AC/分钟

Temperature range:-40°C-+105°C

温度范围: -40°C ~ $+105^{\circ}\text{C}$

Insulation resistance:100MΩ min

绝缘电阻: 100MΩ Min

Contact resistance:10mΩ Max

接触电阻: 10mΩ Max

X2513 H - XX X - NO

① ② ③ ④ ⑤









1.Series No

2. Category: H-Housing

3.Row No.Pin No:XX-02~08P

4.Special No:A-A Key(Black);B-B Key(Natural)

5. Material: N0-PA66 94V-0



Poles	Dimensions(mm)	
	A	B
02	7.70	2.50
03	10.20	5.00
04	12.70	7.50
05	15.20	10.00
06	17.70	12.50
07	20.20	15.00
08	22.70	17.50

X2513H-XXX-N0	PA66	X2513W	X2513T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

DSND		SCALE: N/A	MODEL TYPE: 2.50mm Crimp Style Connector
DWN		VIEW: 	PART NO.: X2513H-XXX-N0
CHKD		UNIT: mm/in	DWG NO.: X-X2513H-XXX-N0
APPD		SIZE: A4	

WEIGHT	SHEET	REVISION
	1/1	A0

					ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5

REVISIONS

UNSPECIFIED TOLERANCES

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

XKLE

XKB INDUSTRIAL PRECISION CO.,LIMITED